

# operating head for cam switch - $\emptyset$ 38 mm - black handle

KAA2H

EAN Code: 3389110980745

#### Main

Range of product	Harmony Series K	
Product or component type	Cam switch operating head	
Component name	KAA	
Product compatibility	Front mounting bodies 12 and 20 A by Ø 22 mm hole	
Cam switch head type	With bezel Ø 38 mm, plastic	
Type of operator	Black handle, length = 35 mm	
Rotary handle padlocking	Without	
Presentation of legend	With mat black legend	

## Complementary

Mechanical durability	1000000 cycles
CAD overall width	38 mm
CAD overall height	38 mm
CAD overall depth	77 mm
Length	35 mm
Product weight	0.048 kg
Compatibility code	КАА

### **Environment**

Protective treatment	TC	
Ambient air temperature for operation	-2555 °C	
Ambient air temperature for storage	-4070 °C	
Shock resistance	30 gn conforming to IEC 68-2-27	
Vibration resistance	5 gn conforming to IEC 68-2-6 (f = 10150 Hz)	
IP degree of protection	IP65 conforming to IEC 529 IP65 conforming to NF C 20-010	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	5.5 cm

Package 1 Length	9.0 cm
Package 1 Weight	58.0 g
Unit Type of Package 2	S01
Number of Units in Package 2	28
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.728 kg

# Logistical informations

Country of origin CZ

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
China RoHS Regulation	China RoHS declaration

#### **Use Again**

○ Repack and remanufacture	
Take-back	No