



Stubby Ball End L-Wrenches



Stubby Ball End Sets L-Wrenches - ProGuard™ Finish

- Fits into tight spaces standard hex keys can not
- Eliminates the need to trim and file the short arm
- Tighter inside radius means full smooth entry into screw head
- Chamfered short arm eliminates burrs
- Ball End inserts into a screw at a 25° angle



High Torque Steel

Up to 20% stronger, with more torque and twice the wear resistance of standard grades of steel



Corrosion-resistant finish: Environmentally safe, provides better tool grip, resists solvents and is 5 times more corrosion resistant than competitor finishes

Cases are color-coded for easy recognition



PART#	MODEL#	PCS	LENGTH	CONTENTS	QTY	SETS
Inch Sets						
16538	SBLX10	10	Long	1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"	1	Inch
16537	SBLX13	13	Long	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8"	1	Inch
Metric Sets						
16592	SBLX7M	7	Long	1.5, 2, 2.5, 3, 4, 5, 6mm	1	Metric
16599	SBLX9M	9	Long	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm	1	Metric

Bondhus Corporation
 1400 E Broadway • PO Box 660 • Monticello, MN 55362
 Tel: 763-295-2162 • Toll Free: 800-328-8310 • Fax: 763-295-4440

Bondhus, Protanium, ProGuard, BriteGuard, GoldGuard and BallStar are trademarks of Bondhus Corporation.

TORX® and TORX PLUS® are registered trademarks of Acument Intellectual Properties, LLC.