



Contactor 63A, 3NO, 230V

ESC363

Technical Properties

Type of contacts	3NO
Override	No
Rated current	63 A
Rated operational voltage Ue	400 V
Frequency	50 Hz
type of connection	with screw
Connection cross-sect. rigid cable	4 / 25mm ²
Connection cross-sect. flexible cable	4 / 16mm ²
Command voltage AC	230 V
Rigid cable connect. cross-sect. for control	1 to 10 mm ²
Max cable connect. cross section (flexible) for control	1 to 6 mm ²
Inrush power absorbed	60 W
Operating consumption	7 W
Number of mechanical operations	100000
Electric endurance in number of cycles	30000
Operating temperature	-10 to 50 °C
Storage temperature	-40 to 80 °C
Protection class	isol.class II
Protection index IP	2
Number of modules	3