

Datasheet for part number M83513/04-D03N

Our Catalog Part Number: M83513/04-D03N
Our Global Manufacturing Part Number: 154175-0012 MS
Brand: Cannon Product Category: Micro Product Line: Micros Series: M83513-1-4

Product Datasheet	
Series	MIL-DLT-83513
Shell Style	Receptacle
Contact Quantity	25
Contact Term Type	Crimp
Contact Gender	Socket
Contact Material	Gold Plated Copper Alloy
Contact Resistance	8 milliohms max.
Length of Wire	18 inches
Shell Material	Metal Shell
Plating	Electroless Nickel
RoHS Compliant	Yes
Insulator	LCP
Current Rating	3 A max.
Dielectric Withstanding Voltage	600 VAC at sea level 150 VAC at 70,00' altitude
Insulator Resistance	5000 megohms min.
Operating Temperature	-55°/+125°
Physical Shock	50 G's, 3 axes, 6 milisecond duration sawtooth pulse
Vibration	20G's, 10-2000 Hz. 12 hours
Durability	500 cycles of mating and unmating, 500 CPH max.
Moisture Resistance	Insulator resistance > 100 megohms
Salt Spray	48 hours
Wire Gauge	#26 Gauge
Wire Type	Per MIL-W-22759/11-26
Wire Color	10 Colors Repeating
Hardware	No Hardware