

Blower LXT

DUB184RT



Product Description

18V LXT • 52,1 m/s • 13,0 m³/min

Efficient brushless blower for demanding use

A versatile, silent and efficient blower for construction and gardening. Equipped with a brushless motor and the tool provides max. air flow of 52,1 m/s and air volume up to 13,0 m³/min at full speed. Includes 1 x 5,0 Ah battery and a charger.

Product Features

- ⦿ Brushless maintenance-free and long-life motor
- ⦿ Three positions for blow volume.
- ⦿ Battery protection system automatically shuts off power when the battery level is low

Barcode

88381887618

Product Specifications

Continuous use 18V / 6.0 Ah battery	12 min
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Tool weight with battery (EPTA)	2,5 - 3,0 kg
Battery Voltage	18 V
Brushless Motor	YES
Sound Pressure Level	86,6 dB(A)
Vibration Uncertainty (K Factor)	1,5 m/s²
Product Dimensions (L x W x H):	825 x 160 x 285 mm
Vibration Level (3 axes)	≤ 2,5 m/s²
Sound Power Level (L _{WA})	93,3 dB(A)
Max. Air Velocity	52,1 m/s
Voltage LXT	1
System	LXT 18V/36V
Product net weight (new)	2,3 kg
Noise Uncertainty (K Factor)	2,7 dB(A)
Tool Category	Dust Management
Air volume	0 - 13,0 m³/min
Blowing force	10,9 N
No load speed	0 - 18000 min ⁻¹
Continuous use 18V / 5.0 Ah battery	10 min

Standard Equipment

- ⦿ 1pc DC18RC Fast Charger
- ⦿ 1pc BL1850B (5.0Ah) 18V LXT Battery

More info

<https://makita.ae/product/blower-lxt-dub184rt/>