

Specifications

Eaton EVMIF132A

Eaton Metered Input G4 Rack PDU, 0U, 39U, IEC-60309 input, 3m cord, 1ph, 7.4kW, 32A, 200-240V, 24 outlets (12)C13, (12)C39



General specifications

PRODUCT NAME	Eaton Rack PDU G4
CATALOG NUMBER	EVMIF132A
MODEL CODE	PDU G4 MI 0U 309 32A 1P 12xC13,12xC39
EAN	3553340697173
UPC	786689801359
PRODUCT LENGTH/DEPTH	1730 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	52 mm
PRODUCT WEIGHT	3.8 kg
COMPLIANCES	CB LVD Directive RoHS Directive WEEE Directive Packaging Directive EMC Directive
CERTIFICATIONS	IEC 62368-1 EN IEC 63000 CISPR 35/EN 55035 CE EAC UKCA Cm Ukr IEC/EN 61000-6-2 IEC/EN 61000-6-4 IEC 61000-3-11 IEC 61000-3-12

Electrical input	
INPUT CONNECTION	IEC-60309 32A 1Ph
WATTAGE	7.4 kW max
AMPERAGE RATING	32 A
INPUT VOLTAGE	200-240V
PHASE	Single-phase
CIRCUIT BREAKER	(2) single-pole
FREQUENCY RATING	50/60 Hz
CORD LENGTH	3m

Electrical output	
OUTLETS	(12) C13, (12) C39
NUMBER OF OUTPUTS C13	12
NUMBER OF OUTPUTS C19	12
NUMBER OF OUTPUTS (OTHER)	12
NUMBER OF OUTLETS WITH EARTH PIN	24

Technology & communications

TYPE	Metered input Rack PDU
-------------	------------------------

OUTLET CONTROL	No
-----------------------	----

SPECIAL FEATURES

- Remote Site Management
- Versatile C39 outlet supports C14 or C20 power cord plug
- High retention outlets designed to securely fit standard power cords and support P-Lock power cords
- Cybersecurity standards UL 2900-1 and IEC 62443-4-2
- Hot-Swap network control module
- Network Cascading, connect up to 32 PDUs via network loop
- Power sharing between two network modules PDUs ensures constant access to PDU data & sensors
- 1% IEC Class 1 billing grade measurement accuracy
- Gigabit network card with 2x Gb ports
- Support protocols RestAPI, Modbus TCP, SNMP, LDAP, HTTPS
- Optional sensor Temperature/Humidity

ETHERNET INTERFACE	Yes
---------------------------	-----

SERIAL INTERFACE	Yes
-------------------------	-----

SNMP	Yes
-------------	-----

MASS CONFIGURATION	Yes
---------------------------	-----

Resources

BROCHURES	Rack PDU G4 Brochure EN
------------------	---

DECLARATIONS OF CONFORMITY	EU declaration of conformity Rack PDU G4
-----------------------------------	--

DRAWINGS	EVMIF132A-en-US
-----------------	---------------------------------

Additional specifications

OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)
------------------------------	---------------------------

ACCESSORIES

- Rack PDU
- Rack mounting accessories
- Quickstart guide
- Safety Instructions

MATERIAL	Aluminium
-----------------	-----------

COLOR	Black
--------------	-------

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

