



SGTM3S10-C



- Low profile design keeps bundle close to mounting surface
- Small overall size allows use where space is limited

• Part Number	SGTM3S10-C
• RoHS Compliancy Status	Compliant
• Part Description	Super-Grip™ Cable Tie Mount - Screw Applied
• Material	Nylon 6.6
• Color	Natural
• Height (In.)	.38
• Height (mm)	9.5
• Length (In.)	.86
• Length (mm)	21.8
• Width (In.)	.61
• Width (mm)	15.5
• Environment	Indoors
• Flammability Rating	UL94 V-2
• Hole Diameter (In.)	.19
• Hole Diameter (mm)	5.0
• Mounting Method	#10 (M5) Screw
• Pricing Description	Super Grip Cable Tie Mount, .88" (22.4mm)W, #10 Screw (M5), Nylon
• Screw Size	#10 (M5)
• Screw Size Metric	M5
• Used With Cable Ties	SGM,SGI,SGS,SGLH
• Min. Order UOM	PC
• Min. Order Qty.	100
• BOM Qty. (# of Pkgs.)	