

Features

- USB 3.0 A-B Feedthrough Connector
- Front or rear mounting through the panel
- Standard Ø24mm cutout hole
- Low rear profile
- No soldering or punch termination. Use standard cable for each connector style

RS PRO USB 3.0 A-B Straight Panel Mount Connector

RS Stock No.: 533-694



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This USB Feed Through connector allows you to connect and adapt different USB types through a sturdy panel mount connection. Suitable for wall plugs and rack mounting, this XLR Format USB adaptor is a valuable tool in connecting custom configurations that use standard cabling, and is commonly used in digital recording studio and network racking.

The connector fits onto standard XLR 24mm diameter cutout panels and is available with various hole types, making rear and front panel-mounting simple. The low rear profile of this connector ensures it's easy to use where space is a constraint, such as in data centres.

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

General Specifications

Connector Type	USB 3.0
Gender	Female
USB Type	A-B
Orientation	Straight
Mounting Type	Panel Mount
Colour	Black

Electrical Specifications

Current rating	1.8A max
Voltage rating	30V AC
Contact Resistance	50mΩ max
Insulation Resistance	20MΩ max
Dielectric withstanding voltage	500V AC

Mechanical Specifications

Mounting Hole	Ø3.5mm Countersunk holes
Frame material	Zinc Diecast, black plated
Insert Material	ABS
Shell material	Nickel plated steel
Contacts	Gold plated

Operation Environment Specifications

Operating Temperature	-20 to +50°C
-----------------------	--------------

Approvals

Compliance/Certifications	RoHS
---------------------------	------

