

Head SPANNFIX for screwing on (M12×1.5)

Art.-No.**9-252****Description**

Head SPANNFIX for screwing on (M12×1.5)

Features

for precision ball joint rotatable 360° steplessly lockable quick release

Quality product 100% Made in Germany

for screwing on ball joint holder 9-251, 9-261, 9-281

50 mm plastic jaws with grip

clamping width 70 mm

clamping depth 38 mm

clamping pressure 1470 N

spare parts: jaws

article 9-900-E50 (pair)

more jaws search field input 9-900

cast aluminum, powder-coated, dark gray metallic

Dimensions approx. 180 × 70 × 50 mm

weight 560 g

**Application and technical data**

Connection thread M12 × 1.5 mm (special thread).

Parts list