

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Heat Gun

GHG 23-66 Professional



Complete temperature and airflow control for demanding applications

Part number: 0 601 2A6 300

[> More product information](#)

Technical Data

webshop-pdp-section-technical-data-table-key-Battery and power

Rated input power	2.300 W
-------------------	---------

webshop-pdp-section-technical-data-table-key-Size and weight

Weight	0,7 kg
Tool dimensions (width)	86 mm
Tool dimensions (length)	245 mm
Tool dimensions (height)	201 mm

Noise/vibration information

Noise

Sound pressure level	70 dB(A)
----------------------	----------



Product data sheet

Power tools for trade & industry

Advantages

- 10 airflow rates, digitally adjustable temperature settings, and 4 customizable programs for total tool control
- Incredibly strong 2300 W motor to quickly reach 650 °C
- Enhanced Safety thanks to the thermal protection:
Automatic shut-off of the heating element in case of motor overheating

