

Han PushPull PFT plastic HIFF



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 012 0331
Specification	Han PushPull PFT plastic HIFF
HARTING eCatalogue	https://harting.com/09350120331

Identification

Category	Connectors
Series	Han® PushPull (V14)
Type of hood/housing	Bulkhead mounted housing

Version

Locking type	PushPull
Details	for all HIFF compatible modules

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-117
	EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	5.96 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140053939
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466