



22218EAE4

Spherical Roller Bearings

Parts Number

22218EAE4C3

Boundary Dimensions

d	90	mm	Bore diameter
D	160	mm	Outside diameter
B	40	mm	Width
r (min.)	2	mm	Chamfer dimension

Basic Load Ratings

Cr	360000	N	Basic dynamic load rating
C0r	395000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	3800	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	5000	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	3200	min-1	Grease lubrication
Oil (Oil-bath)	4000	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	100	mm	Diameter of shaft abutment
da (max.)	108	mm	Diameter of shaft abutment
Da (min.)	142	mm	Diameter of housing abutment
Da (max.)	150	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

e	0.24	Constant
Y2	4.3	Axial load Factors
Y3	2.9	Axial load Factors
Y0	2.8	Axial load Factors

Mass

Mass approx.	3.3	kg	Mass approx.
--------------	-----	----	--------------

