

Datasheet

RS Pro 12V dc, 4A Battery Charger

RS Stock No: **851-7486**



Product Details

RS Pro battery charger is a compact automotive charger with pressed steel case. This UK plug type battery charger yields 12 V dc output voltage at 4 A charge current. It comes with carrying handle that is suitable for regular and low maintenance battery available in 12 V, 6/12 V and 12/24 V versions. This charger has the ability to react to the battery condition and deliver the required charge rate. It is perfect choice for long term care as well as general automotive use.

Features and Benefits

- Trickle and fast charging
- Charging, overload and reverse polarity warning lights
- Ventilation to maintain low working temperature
- Large ammeter display
- Dash mounted fuse for polarity protection
- Rocker switches control variable output to the battery to maintain peak condition
- Suitable for regular and low maintenance batteries
- Supplied with 2200 mm length output cables with heavy duty crocodile clips and is fitted with ASTA/BS approved
- non-rewirable 3-pin safety plug

Specifications:

Battery Type Charged	Lead Acid
Number of Charge Stages	1
Plug Type	UK
Standards Met	ASTA/BS Approved
Charge Current	4 A
Input Voltage	230 V ac
Output Voltage	12 V dc
Output Voltage @ Charge Current	12 V dc at 4 A
Input Frequency Range	50 Hz