

Datasheet

GLASS ROPE LAGGING

RS Stock number 749-5124



Product

Glass Rope Lagging is manufactured from a central core of glass fibre sliver which is contained by an open over-braid of texturized continuous filament glass yarn. The low thermal conductivity offers an ideal and cost efficient method of insulating pipe work.

High temperature flue sealing and caulking applications are also alternative uses for this type of product. The maximum operating temperature recommended is 550 deg C.

Physical Properties

Diameter Coil Size

6mm 30m

8mm 30m

10mm 30m

12mm 5m - 775-7804

12mm 30m - 749-5124

15mm 30m

20mm 5m - 775-7807

20mm 30m - 749-5127

25mm 30m

30mm 30m

Glass Rope Lagging is also available in cut length and "O" ring form produced to customers individual requirements.