

### **FEATURES**

- Pozidriv head type for improved screwdriver grip
- Pan head design for a flat bearing surface
- A2 stainless steel
- Easily Cleanable
- Meets DIN 7985 Standards

# RS PRO, M5 Pan Head, 16mm Stainless Steel Pozidriv A2 304

RS Stock No.: 528-873



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

From RS PRO a high-quality pan head machine screw with a versatile Pozidriv recess for a superior grip when tightening. This machine screw has a metric thread and is made from high-quality A2 stainless steel which has strong abrasion resistance and excellent resistance to corrosion.

## **General Specifications**

Head Shape	Pan
Drive Type	Pozidriv
Applications	Food processing and brewing equipment, Domestic appliances, Building fasteners and fixings, Medical equipment, Non-salt water marine applications

### **Mechanical Specifications**

Thread Size (Metric)	M5
Length Metric	16mm
Material	Stainless Steel
Stainless Steel Type	304 (A2)
Thread Pitch	0.8mm
Head Diameter	9.14mm to 9.5mm
Head Height	3.52mm to 3.7mm
Recess Diameter	2.29mm to 2.74mm
Specification	DIN 7985





RS Part No.	Thread Size	Length
528738	M3	6mm
528744	M3	10mm
528750	M3	12mm
528801	M4	6mm
528817	M4	10mm
528823	M4	12mm
528839	M4	16mm
528845	M4	20mm
528867	M5	12mm
528873	M5	16mm
528889	M5	20mm
528895	M5	25mm





d1		M1.6	M2	M2.5	М3	M3.5	M4	M5	M6	M8
d2		3.20	4.00	5.00	6.00	7.00	8.00	10.00	12.00	16.00
k		1.42	1.72	2.12	2.52	2.82	3.25	3.95	4.75	6.15
Recess	no.	0	1	1	1	2	2	2	3	4

