



ALPHA 630, Floor-mounted cabinet, IP55, Protection class 2, H: 1950 mm, W: 1050 mm, T: 320 mm, RAL 7035

Model	
product brand name	ALPHA
product designation	Free-standing cabinet
surface processing	powder-coated
Protection class	
protection class IP	IP55
operating resource protection class	Safety class 2
IK protection class	IK09
suitability for interaction lightning protection	Yes
suitability for use for outside use	No
Appearance	
RAL color number	7035
product component	
• cable entry	Yes
• mounting plate	No
product extension optional side-by-side mounting	Yes
number of rows	48
Mechanical Design	
height	1 950 mm
width	1 050 mm
depth	320 mm
installation depth	320 mm
number of modular width units	576
number of modular width units per DIN mounting bar	12
fastening method	floor mounting
net weight	75 kg
material of the enclosure	Steel
Approvals Certificates	
General Product Approval	
Test Certificates	



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

other	Environment			
Confirmation	Miscellaneous	Environmental Confirmations	Environmental Confirmations	

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1333-8KN44>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8GK1333-8KN44>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1333-8KN44

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

5/26/2025 

