

### FR28 - Bizflame Work FR Coverall

**Collection:** Bizflame™ Work

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Bizflame Work: 99% Cotton, 1% Carbon Fibre, 280g

**Outer Carton:** 12



### Product information

Constructed using a lighter weight highly innovative flame resistant BizFlame Work fabric.

#### Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

### Standards

EN ISO 11612 (A1+A2, B1, C1, F1)  
EN ISO 11611 Class 2 (A1+A2)  
EN 1149 -5  
EN 17353 Type B2

### Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Action back for extra freedom of movement
- Hook and loop cuffs for a secure fit
- Two tier knee pad pockets allowing two positioning options
- Side access openings
- Sleeve pocket
- Sew on flame resistant industrial wash tape
- Two-way zip for quick and easy access

**FR28 - Bizflame Work FR Coverall**  
**Commodity Code: 6211321000**

**Test House**

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
 Bracetown Business Park  
 D15 YN2P, Ireland  
 Cert No: 2777/13017-03/E00-00

**Wash Care**



**Carton Dimensions/Weight**

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
FR28NARXS	Navy	43.0	28.0	46.0	1.2600	0.0554	5036108202546	15036108688200
FR28NARS	Navy	43.0	28.0	46.0	1.2500	0.0554	5036108183111	15036108625564
FR28NARM	Navy	43.0	28.0	46.0	1.3200	0.0554	5036108183104	15036108625557
FR28NARL	Navy	43.0	28.0	46.0	1.4300	0.0554	5036108183098	15036108625540
FR28NARXL	Navy	43.0	28.0	46.0	1.4400	0.0554	5036108183128	15036108625571
FR28NARXXL	Navy	43.0	28.0	46.0	1.5300	0.0554	5036108183135	15036108625588
FR28NARXXXL	Navy	43.0	28.0	46.0	1.5900	0.0554	5036108183142	15036108625595
FR28NAR4XL	Navy	43.0	28.0	46.0	1.5900	0.0554	5036108197644	15036108683656
FR28NAR5XL	Navy	43.0	28.0	46.0	1.7800	0.0554	5036108217571	15036108704764