Blacklight BL368 Linear & Circline

F20W/T12/BL368

0000361

Produkteigenschaften

- BL368 tubes emit an upgraded highly concentrated radiation with peak around 368 nm. Flying insects eye sensitivity is generally at or near this frequency
- 100% improvement in effectiveness (at 368nm)
- Depreciation of UV-A output over time is significantly reduced (80% at 5000hrs of original 100 hour output)
- Performs longer and better throughout the insect season
- Same shape, structural and electrical characteristics and control circuits as standard T12,T8 or T5 tubes
- Applications
- Insect traps, insect attraction is strongly increased
- Restaurants, kitchens, food shops, supermarkets
- Diazo printing machines
- Photo Polymerisation
- Chemical processing
- Mineral detection
- Various technical applications
- Directions for use
- Maximum exposure limits are set by EN60335-2-59:1997 at an effective 1.0 milliWatt per metre squared (1.0 mW/m²) measured at a distance of 1 metre originally based on the recommendations of the National Radiological Protection Board in the UK. The irradiance value for a single BL368-lamp measured without reflector and/or fixture, in free air at 25 celsius, is varying between 0.2 and 0.4 mW/m² depending on the wattage

PRODUKTÜBERSICHT

Bestellnummer	0000361
Lampenform	Tubular
Lampenoberfläche	Coated
Dimmbar	Yes
Verschluss/Sockel	G13
Typ	T12-Special
EAN-Code	5410288003610
Watt (Nennleistung) (W)	20
Spannung (V)	57

Blacklight BL368 Linear & Circline

F20W/T12/BL368

0000361

DATENTABELLE

Allgemeine daten

Bestellnummer	0000361
Mittlere Lebensdauer (Nennwert) (h)	10000
Lampenform	Tubular
Lampenoberfläche	Coated
Dimmbar	Yes
Verschluss/Sockel	G13
Typ	T12-Special
EAN-Code	5410288003610
E-Nummer FI	4940433
Lange Bezeichnung	BL368 tubes emit an upgraded highly concentrated radiation with peak around 368 nm. Flying insects eye sensitivity is generally at or near this frequency. 100% improvement in effectiveness (at 368nm). Depreciation of UV-A output over time is significantly reduced (80% at 5000hrs of original 100 hour output). Performs longer and better throughout the insect season. Same shape, structural and electrical characteristics and control circuits as standard T12,T8 or T5 tubes. Applications. Insect traps, insect attraction is strongly increased. Restaurants, kitchens, food shops, supermarkets. Diazo printing machines. Photo Polymerisation. Chemical processing. Mineral detection. Various technical applications. Directions for use. Maximum exposure limits are set by EN60335-2-59:1997 at an effective 1.0 milliWatt per metre squared (1.0 mW/m²) measured at a distance of 1 metre originally based on the recommendations of the National Radiological Protection Board in the UK. The irradiance value for a single BL368-lamp measured without reflector and/or fixture, in free air at 25 celsius, is varying between 0.2 and 0.4 mW/m² depending on the wattage
Produktname	F20W/T12/BL368
Quecksilbergehalt der Lampe (mg)	10
Betriebsgerät erforderlich	Yes
Leuchtennennwert	Open
IEC-Referenz	IEC 60081
IEC-Referenz 2	IEC 61195
Lampen für spezielle Einsatzbereiche	Yes
Transformator erforderlich	No
Menge/Verpackungseinheit	25

Elektrische daten

Watt (Nennwert) (W)	20
Watt (Nennleistung) (W)	20
Spannung (V)	57
Stromstärke (A)	0.37

Blacklight BL368 Linear & Circline

F20W/T12/BL368

0000361

Physikalische daten

Gewicht (kg)	0.14
Länge Basis zu Basis (mm) – A	589.8
Länge Basis zu Pin (Min-Max) – B	594.5-596.9
Lampenlänge (mm) – C/L	604
Lampendurchmesser (mm) – D	38
Verpackungsbezeichnung	Box/Sleeve
Single package dimensions (L x W x H) (cm)	60.30 x 4.30 x 4.10
Outer package dimensions (L x W x H) (cm)	63.00 x 22.00 x 21.00

Blacklight BL368 Linear & Circline

F20W/T12/BL368

0000361

TECHNISCHE ZEICHNUNGEN