


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	MATERIAL	HEADER COLOR	FEET PER ROLL
T400X000YX1	GMYTHERM-900W	ORANGE	50
T400X000A91	GMYTHERM-900W	RED	50

NOTES:  
1. DIMENSIONS IN [ ] ARE MILLIMETERS

CAD FILENAME/LAYERS 100472HH-DC-C10632/08F

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	PANDUIT CORP. TINLEY PARK, ILLINOIS			
5	12/1/11	RVU		CHANGED FROM T400X000YZ1 TO T400X000A91.	6583	R			T400X000YX1 THERMAL TRANSFER ARC FLASH TAPE			
4	10-05-11	DLI		ADDED TABLE, REMOVED COLOR LEADER.	6540	R						
3	05-08-08	JHAC		REMOVED TABLE AND CHANGE NOTE 1 CHANGED SECONDARY UNITS ON LENGTH	5404	R			UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1 (.XXX) ± .031 (.XX) ± .05 ANGLES ± 1°			
2	12-06-05	RVU		MOVE PRINT TO OPPOSITE SIDE.	0000	R					UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
1	10-6-05	RVU	DWY	ADDED UNDERScore AND DIM. .125"; REVISED STRIPE WIDTH FROM 1.250" TO 1.25 ± .031". ADDED NOTE 2.	4218	R			DRAWN BY RVU	MAT'L: GM4-HT* POLYESTER	SCALE NTS	
0	8-3-05	RVU	DWY	DRAWING RELEASE	4106	R			DATE 8-3-05		DRAWING NO. C10362	DWG SIZE A
									CHK'D <i>[Signature]</i>			