

---

## GSR 12-2 Professional

---



Cordless drill/driver

### **GSR 12-2 Professional**

Compact tool for universal use

- 2-speed
- 25 torque settings
- 2 battery packs

- Softgrip
- Compact dimensions

Part no. 0 601 918 J70

- 2 x 1.5 Ah NiCd batteries
- 1-h charger
- Carrying case

#### Technical data

Torque, max. (hard screwdriving applications)	27 Nm
Torque, max. (soft screwdriving applications)	11 Nm
No-load speed (1st gear/2nd gear)	0 – 400 / 1.200 rpm
Battery type	NiCd
Chuck jaw width, min./max.	1 / 10 mm
Battery voltage	12 V
Battery capacity	1,5 Ah
Charging time, approx.	60 min
<b>Screw diameter</b>	
Max. screw diameter	7 mm

#### Functions

- Forward/reverse operation
- Softgrip

#### Noise/vibration information

##### Show values

Measured values determined according to EN 60745.  
Total vibration values (vector sum of three directions)

##### Drilling in metal

Vibration emission value ah	2,5 m/s <sup>2</sup>
-----------------------------	----------------------

Uncertainty K	1,5 m/s <sup>2</sup>
---------------	----------------------

---

**Screwdriving**

---

Vibration emission value ah	2,5 m/s <sup>2</sup>
-----------------------------	----------------------

Uncertainty K	1,5 m/s <sup>2</sup>
---------------	----------------------

The A-rated noise level of the power tool is typically as follows: Sound pressure level 80 dB(A); Sound power level 91 dB(A). Uncertainty K= 3 dB.

