



PRODUCT-DETAILS

UPS PowerValue 11LI Up 1000 VA

UPS PowerValue 11LI Up 1000 VA



General Information	
Extended Product Type	UPS PowerValue 11LI Up 1000 VA
Product ID	4NWP100172R0001
EAN	7640169262623
Catalog Description	UPS PowerValue 11LI Up 1000 VA
Long Description	VI UPS PowerValue 11LI Up 1000VA/600W:230V:50/60Hz:simulated sinewave:3 min

Material Compliance	
Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD004620
RoHS Information	4NWD004317
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	ea68414c-d4fb-433b-ba08-4a03c1614670 Switzerland
Simplified SCIP	32512457-2146-4c11-81aa-a2afc6bb3e5d Germany 1cf08ede-f99d-48f5-82e7-6eb5c103825d Czech Republic 48c997c9-2bda-4851-a61e-2569006b9ea9 Poland e8e5abd5-c46a-4c31-a88c-a6965b271915 Netherlands f178479b-2f07-47b8-9573-8b057e0425da Netherlands ff30f193-b61f-4250-a471-e883785efe0a Germany

13fd1aa1-b6c3-4ae4-ae65-dca4d28c1a93 Denmark
b51a002d-8f0f-405c-8dee-bf8776524277 Poland
d650f526-3faf-4c06-9c2e-840f832ecd23 Norway
e21bc697-77bb-4863-8df9-494ebae2a596 Finland
e7c6b406-b451-4753-b2d6-c8408e9ffa73 Netherlands
4617a0de-5f2d-468e-9303-2fc8957ed5f9 Germany
6f92732b-3eb7-4c54-aec0-4598e126703e Croatia
991e409f-4791-46bf-aaa4-63d0236045a3 Poland
1683c4fd-2f72-4387-9477-b874c926b147 Germany
795c06db-3c22-4804-955e-a325edacaf92 Germany
79d4b102-3145-4e87-8ad6-9929c2a02237 France
05b15f8c-0ed4-4777-85a9-794aa166cbc8 Netherlands
361649d8-f616-4315-bbb0-b2f8cf7c3b1d Spain
6c9074e3-240b-4028-99e2-33d69a3b6180 Netherlands
11e855a2-f858-415e-bd31-3d66fafa5b4f Estonia
8be49968-68cc-4066-8624-97c1e6f190bb Greece
5f28e5b4-6e34-48d4-bebd-84638224bce0 Portugal
13ac629f-e65b-487a-8515-394fa47b5259 Bulgaria
372793f0-0694-41aa-8e76-4804a26aac51 Sweden
d24a5b00-6b48-4873-9dca-90f372f1380b France
9ef7587c-95f9-4cb2-a638-cc33caa21c3c Sweden

Popular Downloads

Data Sheet, Technical Information	4NWD004445_ML
Instructions and Manuals	4NWD004445_ML

Environmental

Ambient Air Temperature	Storage -15...+60 °C
Environmental Information	No declaration needed

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Norway)	6600714
Country or Territory of Origin	China

Dimensions

Product Net Width	145 mm
Product Net Height	190 mm
Product Net Depth / Length	335 mm
Product Net Weight	7.5 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	228 mm
Package Level 1 Height	287 mm
Package Level 1 Depth / Length	410 mm
Package Level 1 Gross Weight	10 kg
Package Level 1 EAN	7640169262623

Technical

Apparent Power Output	1000 V·A
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.1 kg
Communication Interface	USB, RS-232
Connection Type	IEC C14
Display Type	LCD
Input Voltage (U_{in})	230 V
Input Voltage Type	AC
Number of Batteries	2
Number of Outputs	C13 Connection 6
Number of Phases	1-phase Primary 1-phase Secondary
Options Provided	Auto shut down function
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Rated Output Power	600 W

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004317

External Classifications and Standards

ETIM 9	EC000382 - UPS
ETIM 10	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 LI IEC 230V

