

**KEMET Part Number: SMR7.5474J100K04L16.5CBULK**  
(F211KM474J100ALG5C)

SMR/F211, Film, Metallized PPS, General Purpose, 0.47 uF, 5%, 100 VDC, 125°C, Lead Spacing = 7.5mm



**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	SMR/F211
<b>Dielectric:</b>	Metallized PPS
<b>Style:</b>	Radial
<b>Features:</b>	Audio Applications
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Miscellaneous:</b>	The rated voltage decreases 2%/C between +125C and +150C
<b>Notes:</b>	Case Size = KM

**Dimensions**

<b>L</b>	10.5mm MAX
<b>H</b>	12mm MAX
<b>T</b>	6mm MAX
<b>S</b>	7.5mm +/-0.4mm
<b>LL</b>	16.5mm +0.5mm
<b>F</b>	0.6mm +/-0.05mm
<b>G</b>	0.5mm NOM

**Specifications**

<b>Capacitance:</b>	0.47 uF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage AC:</b>	63 VAC
<b>Voltage DC:</b>	100 VDC
<b>Temperature Range:</b>	-55/+150C
<b>Rated Temperature:</b>	125°C
<b>Dissipation Factor:</b>	0.15% 1kHz, 0.25% 10kHz, 0.6% 100kHz
<b>Insulation Resistance:</b>	10.6383 GOhms
<b>Max dV/dt:</b>	15 V/us

**Packaging Specifications**

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	1000