

Features

- Especially suitable for plant construction, logistics and general industrial requirements
- For universal audible applications
- Well-designed electromechanical horn
- Typical horn tone 92dB
- 24V DC operation

RS PRO Sounder

RS Article.: 0658308



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Aesthetically designed electromechanical alarm horn that is used in various industries.
- Generally used to signal faults or dangerous situations acoustically.
- This electromechanical horn without cone provides high-quality audible signalling.
- A steady high-volume tone of 92dB is provided.
- IP43 degree of protection suitable for 24V DC supply voltage requirements
- Easily mounted onto a wall via 2 screws with cable entry to the rear

General Specifications

Housing	ABS grey (RAL 7035)
Type of Mounting	Wall mounting. Sound outlet opening at bottom
Fitting	2 bolts / screws
Magnetic Type	No
Cable Entry	Back
Connection	Terminal up to 2.5mm ²
Tone	Steady Tone
Duty Cycle	100%

Mechanical Specifications

Dimensions	75mm (w) x 80mm (d) x 72mm (h)
Mounting Style	Screw Mount
Weight	150g

Electrical Specifications

Supply Voltage	24V DC
Volume	92 dB
Current Type	DC
Current Consumption	26mA

Protection Category

IP Rating	IP43
-----------	------

Operation Environmental Specifications

Maximum Temperature	+50°C
Minimum Temperature	-25°C

Approvals

Compliance/Certifications	CE
Declarations	RoHS Compliant / REACH

