

111CM Wide opening adjustable wrenches, chrome-plated, short series


The new wide opening adjustable wrench, Beta 111CM, allows differently sized nuts and bolts to be tightened and loosened through the sliding jaw, which can be adjusted through the central roll.

Features:

- Head angled at 15 degrees, allowing hardly accessible spaces to be reached
- Wide wrench opening, even with extremely short wrench
- Compact head with completely open jaw
- Right-hand rotation
- Double laser marking in mm/inches
- Matt chrome-plated heads for improved scale readout
- Matt chrome-plated body
- Made from high-performance alloy steel for increased mechanical torsional strength
- Special heat treatment for excellent wear resistance
- Coated handle for optimized comfort and increased hold
- Hole on handle for hanging wrench

Extra wide jaw opening

Compact sizes

	art.				
001110770	111CM 170	170	6	32	240
001110722	111CM 220	220	8	38	327
001110727	111CM 270	270	10	46	692

