

## **A-10 ; 0...400 bar gauge; 4...20 mA, 2-W @ 8...30 V DC**

### **Pressure transmitter Model A-10**

Item number:	12751198	
Quantity:	1 pcs.	
Order code:	A-10-6-BG540-HD1Z-AA-M4Z-ZW 2BZZZSAZZZA3Z	W1011A10Z-SZ3S-ZZFZPA-
Overview:	A-10 ; 0...400 bar gauge; 4...20 mA, 2-W @ 8...30 V DC Pressure transmitter Model A-10 Non-linearity: 0.5% BFSL Process connection: G 1/4 A DIN EN ISO 1179-2; Sealing: NBR Electrical connection: circular connector M12x1, 4-pin Pin assignment: U+=1, U-=3 Permissible medium temperature: 0...+80 °C Approvals: cULus Type of packaging: folding box single WIKA standard - specification according to data sheet PE 81.60	
Details:	Pressure transmitter Model A-10 for general applications Specifications according to data sheet: PE 81.60 Wetted parts: 316L Case: 316L Non-linearity: 0.5% BFSL Unit: bar Pressure type: gauge Measuring range: 0...400 bar gauge Process connection: G 1/4 A DIN EN ISO 1179-2 Sealing: NBR Permissible medium temperature: 0...+80 °C Output signal: 4 ... 20 mA, 2-wire Power supply: 8...30 V DC Electrical connection: circular connector M12x1, 4-pin Approvals: cULus W1 (Wika standard) Customer address: <a href="http://www.wika.com">www.wika.com</a> Model name customer-specific: A-10 Pressure port: Standard Type of packaging: folding box single Test protocol: with test protocol Main Language: English Pin assignment: U+=1, U-=3 Customer-specific: WIKA standard - specification according to data sheet Model: A-10 2.0 Operating Instructions: with printed OI	

Date: 22/01/2024



Additional Data: without