



1060

Micro

The Peli 1060 Micro Case is perfect for protecting small electronic devices and other valuables when you're on the road. This small protective case comes with a handy carabiner clip, clip closure on the front of the case, automatic purge valve and a rubber liner that provides protection and also acts as a sealing gasket. The case is waterproof, dustproof and shockproof.

- **Available in clear with color liner or solid**
- **Watertight, crushproof, and dustproof**
- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Carabiner
- Easy open latch
- Rubber liner for extra protection doubles as o-ring seal
- Peli's legendary lifetime guarantee**
- * Where applicable by law



DIMENSIONS

Interior (L×W×D)	8.25 x 4.25" x 2.25 (21 x 10.8 x 5.7 cm)
Exterior (L×W×D)	9.88 x 5.59" x 2.63 (25.1 x 14.2 x 6.7 cm)
Lid Depth	0.69" (1.8 cm)
Bottom Depth	1.44" (3.7 cm)
Total Depth	2.13" (5.4 cm)
Int Volume	0.05 ft³ (0.001 m³)

MATERIALS

Body	Polycarbonate (PC)
Latch	Xylex
O-Ring	Thermoplastic Rubber
Pins	Stainless Steel
Foam	TL - 426 4 lb. Esther
Purge Body	Polycarbonate (PC)
Purge Vent	Polyester Spun-Bond ePTFE Oleophobic

COLOURS

Black	Blue	Red	Yellow
Black - Clear	Yellow - Clear		

WEIGHT

Weight With Foam	1.03 lbs (0.47 kg)
Weight Empty	1.00 lbs (0.45 kg)
Buoyancy	2.49 lbs (1.13 kg)
Master Pack Weight	7.08 lbs (3.21 kg)

TEMPERATURE

Minimum Temperature	-10°F (-23.3 °C)
Maximum Temperature	199°F (92.8 °C)

CERTIFICATIONS

IP67

OTHER

Minimum Pack	6
Master Pack	6
Military	yes

ACCESSORIES



1062
Pick N Pluck™ Foam Insert

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 08-19-26