





Couplings**6600-Series**

	Body Size	Connection A	Hex mm	L mm	D mm	D1 mm	Weight gr.	Max. Operating Pressure	Part Number
 Female BSPP Thread	1/4"	1/4"	22	49	27		123	350 bar	6603-4-4
	3/8"	3/8"	27	56	31,8		180	280 bar	6603-6-6
	1/2"	1/2"	32	71	38,1		309	280 bar	6603-8-10
	3/4"	3/4"	41	85,5	47,6		624	280 bar	6603-12-12
	1"	1"	48	104	54		842	280 bar	6603-16-16

Plugs**6600-Series**

	Body Size	Connection A	Hex mm	L mm	D mm	D1 mm	Weight gr.	Max. Operating Pressure	Part Number
 Female BSPP Thread	1/4"	1/4"	19	34,5	22	11,8	39	350 bar	6605-4-4
	3/8"	3/8"	22	38,1	25,5	17,2	55	280 bar	6605-6-6
	1/2"	1/2"	27	49,3	31	20,5	97	280 bar	6605-8-10
	3/4"	3/4"	35	57,9	40,3	29	217	280 bar	6605-12-12
	1"	1"	41	70,5	47,5	34,3	330	280 bar	6605-16-16

Dust Protection**6600-Series**

	Body Size	Version	Color	Part Number
	1/4"	for coupling	Red	6659-4PL
	3/8"	for coupling	Red	6659-6PL
	1/2"	for coupling	Red	6659-8PL
	3/4"	for coupling	Red	6659-12PL
	1"	for coupling	Red	6659-16PL
	1/4"	for plug	Red	6657-4PL
	3/8"	for plug	Red	6657-6PL
	1/2"	for plug	Red	6657-8PL
	3/4"	for plug	Red	6657-12PL
	1"	for plug	Red	6657-16PL