

# Data sheet

Single Solenoid/Spring Return 5/2 and 3/2 NAMUR interface solenoid valve.



## Technical Data

- Maximum Operating Temperature: +50°C
- Minimum Operating Temperature: -10°C
- Solenoid power consumption: 3W
- Pressure Range: 2 to 10 bar
- Maximum Flow: 1250 lpm

\*Solenoid Voltage dependent on coil used.

**RS Stock Number : 784-0044**

**G 1/4 NAMUR Solenoid-Spring Valve, 5/2**

**Solenoid Voltage – 12Vdc, 24Vdc, 110Vac, 230 Vac**