

## P350 - FFP3 Dolomite Fold Flat Respirator (Pk20)

**Collection:** Disposable Mask FFP3

**Range:** Disposable Masks

**Materials:** PP, PU Foam

**Inner Pack:** 20

**Outer Carton:** 24

### Product information

Unvalved, vertical, flat folded disposable respirator mask with each mask inside packed into an individual polybag for easier storage. Adjustable nose clip for optimised fit and comfort.

### Disposable Mask FFP3

Disposable mask FFP3 level, protects against solid and liquid particles of high toxicity. Minimal % of filtration 99%. Protects up to 20 times the TLV (Assigned Protection Factor for FFP3 masks) or up to 50 times TLV (Nominal Protection Factor for FFP3 masks). Examples of applications: Sanding of hard wood (beech, oak) / treatment of wood using copper, chrome or arsenic based products / impact stripping of paint / sanding of cement. Exceptional quality and performance are ensured across our range of disposable masks.

### Disposable Masks

Our Biztex® brand ensures exceptional quality and performance across our full range of disposable masks. The extensive Biztex® range offers a high level of protection and quality safeguarding the wearer against many workplace risks including liquid chemicals, static electricity, dry particles and radioactive contamination. The complete Biztex® range includes disposable masks and limited-life garments.

### Standards

EN 149:2001 +A1:2009 FFP3 (NR D)



### Features

- Special compact vertical fold-flat design
- Ultrasonic welded head straps
- Individually wrapped inside hygienic polybag
- Toggle adjusters on each head strap to ensure the optimum fit
- Adjustable nose bar for improved fit and reduced fogging of glasses
- Foam padding around the nose bridge for additional comfort
- Retail box which aids presentation for retail sales
- Individually packed for vending machines
- Dolomite optional clogging test (D) to provide more comfortable breathing and longer lasting filtration performance
- CE certified
- UKCA marked

**P350 - FFP3 Dolomite Fold Flat Respirator (Pk20)**  
**Commodity Code: 6307909311**

**Test House**

BSI Group The Netherlands B.V. (Notified Body No.: NB: 2797)  
John M. Keynesplein 9  
, The Netherlands  
Cert No: CE 783116

BSI Assurance UK Ltd (Notified Body No.: AB: 0086)  
The British Standards Institution  
MK5 8PP, United Kingdom  
Cert No: UKCA 783117

**Carton Dimensions/Weight**

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
P350WHR	White	65.0	44.0	38.0	0.2500	0.1087	5036108360499	25036108849189