


## 9580 Max. 9 VA

### AC/AC ADAPTER

- Max 9 VA output power
- 230 VAC input voltage
- Available with EU or UK terminals
- Compliance with relevant worldwide safety standards
- Exchangeable output plugs, providing:
  - reduced stocking requirements
  - short delivery lead times
  - snap-locks for added safety



<b>Technical specifications</b>	<b>9 V</b>	<b>9 V</b>	<b>9 V</b>	<b>12 V</b>
Input voltage:	230 VAC, 50 Hz			
Output voltage:	9VAC	9VAC	9VAC	12VAC
Max.output power:	3VA	7VA	9VA	6VA
Load current:	300mA	800mA	1000mA	500mA
Temperature range:	-10°C to +40°C			
Protection:	Protected against internal short circuit by thermal fuse in primary			
Insulation class	II			
Electrical safety	EN 60950			
EMC, Emission	EN 61000-6-3			
EMC, Immunity	EN 61000-6-1			
Mains connections:	EU or UK			
Output terminals:	Secondary cable w/snap-on plugs			
Dimensions (EU mod):	56x44x37mm	63x51x42mm	63x51x42mm	
Dimensions (UK mod):	59x51x41			
Weight: UK	230g			
Weight: EU	180g	250g	250g	250g