

Start Waterproof LED G3 fixed output

START WATERPROOF LED G3 1200MM S 6K

0048638



Product features

- Start Waterproof, integrated LED weatherproof luminaire, with UV stabilized flat diffuser and linear prisms designed to achieve uniform lit appearance, optimise light output and to reduce glare, stainless steel diffuser clips and fixing brackets for surface mounting. Polycarbonate housing, Polycarbonate diffuser, 2900 lm, 22 W, 132 lm/W, 6500 K, drive current 350 mA, non dimmable, CRI80, IP65, IK08, Class I, nominal average lifetime (h): 50000, 1278 mm x 84 mm x 75 mm, energy class: A++ A+ A



PRODUCT OVERVIEW

IPC Code	0048638
Product name	START WATERPROOF LED G3 1200MM S 6K
Technology	LED
Housing	Polycarbonate
Mount	Ceiling Mounting and Suspended Mounting
Fixture rating	Enclosed
General application	Logistics & Industry
Certifications	EUNEW009
ETIM Class	EC000109
Fixture luminous flux (lm)	2900
Luminaire efficacy (lm/W)	132
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Beam Angle (°)	100
Photobiological Risk Group	RG1
Total power consumption (W)	22
Electrical protection	Class I
Control gear type	Electronic (constant current)
Dimmable	No
Average life (Nominal) (h)	50000
Housing colour	Grey
IP rating	IP65
IK rating	IK08
Product EAN number	5410288486383
Lamps	Yes
Included lamp	INTEGRATED LED

DATA TABLE

General data

IPC Code	0048638
Product name	START WATERPROOF LED G3 1200MM S 6K
Technology	LED

Start Waterproof LED G3 fixed output

START WATERPROOF LED G3 1200MM S 6K
0048638

Housing	Polycarbonate
Mount	Ceiling Mounting and Suspended Mounting
Fixture rating	Enclosed
General application	Logistics & Industry
Operating Temperature Range (°C)	-20°C to +40°C
Certifications	EUNEW009
ETIM Class	EC000109

Optical data

Fixture luminous flux (lm)	2900
Luminaire efficacy (lm/W)	132
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Beam Angle (°)	100
Distribution type	Direct
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	22
Mains voltage (V)	220-240V~
Mains frequency (Hz)	50/60Hz
Electrical protection	Class I
Control gear required	No
Control gear type	Electronic (constant current)
Dimmable	No
Drive current (mA)	350
Inrush Current (A)	4
Inrush Duration (µs)	32
Glow Wire Test (°C)	850
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	70
Max. Luminaires per 13A C Breaker	90
Max. Luminaires per 16A C Breaker	110
Max. Luminaires per 20A C Breaker	140
Max. Luminaires per 10A B Breaker	60
Max. Luminaires per 13A B Breaker	80
Max. Luminaires per 16A B Breaker	100
Max. Luminaires per 20A B Breaker	125

Lifetime data

Lumen maintenance - L70 B50	60000
Lumen maintenance - L70 B20	60000
Lumen maintenance - L70 B10	60000
Lumen maintenance - L80 B50	60000
Lumen maintenance - L80 B20	60000
Lumen maintenance - L80 B10	60000
Lumen maintenance - L90 B50	59000
Lumen maintenance - L90 B20	53000

Start Waterproof LED G3 fixed output START WATERPROOF LED G3 1200MM S 6K 0048638

Lumen maintenance - L90 B10	50000
Average life (Nominal) (h)	50000

Physical data

Housing colour	Grey
IP rating	IP65
IK rating	IK08
Diffuser finish	Clear
Diffuser material	Polycarbonate
Nominal Product Length (mm)	1278
Nominal Product Width (mm)	84
Nominal Product Height (mm)	75
Weight (kg)	1.61


Packaging

Single packaging type	Carton
Product EAN number	5410288486383
Packaging single length / height (cm)	137.2
Packaging single width (cm)	8.8
Packaging single depth (cm)	8.4
DUN14 (outer)	05410288486383
Units per outer package	1
Packaging outer length / height (cm)	137.2
Packaging outer width (cm)	8.8
Packaging outer depth (cm)	8.4

Safety data

Dry applications use only	No
---------------------------	----

PHOTOMETRY



Distance (m)	Cone diameter (m)	Beam angle (°)	Beam diameter (m)	Illuminance (lx)
0.5	1.40 1.25	102.8° 109.0°	54.5" 51.4"	3942 336
1.0	2.80 2.51	102.8° 109.0°	54.5" 51.4"	985 57
1.5	4.21 3.76	102.8° 109.0°	54.5" 51.4"	433 43
2.0	5.61 5.01	102.8° 109.0°	54.5" 51.4"	246 24
2.5	7.01 6.26	102.8° 109.0°	54.5" 51.4"	155 15
3.0	8.41 7.52	102.8° 109.0°	54.5" 51.4"	109 11

Distance (m) Cone diameter (m) Illuminance (lx)
C0 - C180 (Half beam angle: 102.8°)
C90 - C270 (Half beam angle: 109.0°)

TECHNICAL DRAWINGS

Start Waterproof LED G3 fixed output START WATERPROOF LED G3 1200MM S 6K 0048638



SYLVANIA 0048638

 This luminaire contains built in LED lamps.


 } LED

The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built in LED lamps.


 } LED

The lamps cannot be changed in the luminaire.

SYLVANIA 0048638  874/2012



Start Waterproof LED G3 fixed output
START WATERPROOF LED G3 1200MM S 6K
0048638
