

Technical data sheet

Article number:
924-00501

CE5

Product Group	Closed End Connectors
Product Family	Bootlace Terminals
Material	Aluminium (AL), Polyamide 6.6 (PA66)
Colour	Transparent (CL)
Application Range	Low Voltage
Conductor Size Range mm ²	4.0-6.0 mm ²
Diameter (D)	10.5 mm
Length (L)	25.5 mm
Length (L2)	15.7 mm
Max Voltage	600 V
Operating Temperature	+105 °C
Package Content	25 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	7 mm

