



Save as PDF



3315 LED Zone 0 Flashlight



HIGH POWER

HIGHEST SAFETY

The new 3315Z0 LED light: the lightweight compact design houses 3AA batteries that power a single LED for 110 lumens of super bright LED light. Safety approved for the most volatile work environments ATEX Cat. 1 (Zone 0), the 3315Z0 LED light is one of the most efficient torches on the market today.

The new 3315Z0 LED light:

Compact light, huge LED performance.



3315 LED Zone 0 Flashlight

ANSI FL1 Specifications

LIGHT SOURCE	High	
	LED	
BATTERIES	3 AA Alkaline (Included)	
CHARGE TIME	N/A	
VOLTAGE	4.5	
LENGTH	15.6 cm (6.14")	
WEIGHT W/ BATTERIES	0.13 kg (4.5 oz.)	
WEIGHT W/O BATTERIES	0.1 kg (3.7 oz.)	

Materials

Body	Lens	Shroud	Switch Type
High Impact ABS	PC		Push button On/Off body switch
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film
		EPDM	

Configuration

Cat. #	Description
3315Z0	3315 LED Zone 0 Flashlight

3315 LED Zone 0 Flashlight Accessories

No accessories are currently available for this product

LIGHT OUTPUT

RUNTIME (hours/min)

BEAM DISTANCE (meters)

PEAK BEAM INTENSITY (candela)

FL1 STANDARD	High	
	19h	
	164m	
	6698cd	

Approvals

CE Ex - II 1 G Ex ia IIC T4 Ga, II 1 D Ex ia IIIC T130°C

Da

Certificate: TRAC13ATEX0009X