




Datasheet

ENGLISH

Stock No: 130-634

RS Pro Plain Stainless Steel Pan Head Machine Screws, M4 x 30mm



Product Details

Metric Thread, A2 Stainless Steel Slot Pan Head Machine Screw

Machine screws are fully threaded and can be used in pre-tapped holes or used with conforming nuts and washers in through holes.

Our RS Pro slotted, pan head machine screws have been designed to give you ease of assembly.

Features and Benefits

Typical Applications

- Good corrosion resistance
- Recyclable
- Non-magnetic
- Can be used up to 800°C
- Medical
- Most food applications
- Construction
- Domestic



ENGLISH

Note

Requires a flat head screwdriver

We offer a range of slotted pan head machine screws in various thread sizes and lengths. Refer to the datasheet and range overview download file for details.

If A2 (304) stainless steel is not what you are looking for, we can also offer you the fasteners in steel and brass. We also offer the slotted machine screws in A4 (316) stainless steel, steel and nickel plated brass. Refer to the fasteners selection guide for details.

Standards

Threaded in accordance with DIN 85

Specifications:

Length	30mm
Thread Size Metric	M4
Head Shape	Pan
Material	Stainless Steel
Drive Type	Slot
Stainless Steel Type	A2, 304
Finish	Plain