Inflator LXT®

DMP181

18V • 11,1 bar • 161 psi

Powerful LXT® air pump for example filling tyres for cars and bicycles.

DMP181 18V LXT® air pump is based on DMP180 but with higher maximum pressure.It automatically stops inflating when the preselected air pressure level is reached. Includes several valves for filling different types of products - eg footballs, tyres, etc.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Maximum Flow Rate	22 L/min
Max Pressure	11,1 bar
Hose length	0,65 m
Sound Pressure Level (L_{pA})	73 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	3,6 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Tool weight with battery	2,5 - 2,8 kg
Product Dimensions (L x W x H):	316 x 108 x 231 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion

User benefits

- Ideal for inflating tyres of cars and bicycles, sport balls, and more
- Excess air can be released by pressing and holding the air release button
- Digital pressure gauge with added convenient functions
- The machine stops automatically when target pressure is reached
- The machine remembers the pressure setting last time you power off
- 3 Inflation modes (High speed, Low speed or Ball modes)
- Comes with various kinds of valve adapters
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com

Related products

Other

User manual

Parts drawing