

Dimensions(mm)




Specification

Nominal voltage(V)	3
Nominal capacity(mAh)	120
Continuous drain(mA)	0.03
Operating temperature(°C)	-30 to +80

Discharge temperature characteristics








Capacity vs. load resistance

Chapter 2-28

Panasonic 2006



Chapter 2 Poly-carbonn

* The data in this document are for descriptive purposes only and are not intended to make or imply any guarantee or warranty.