

## Parallel female thread coupler



### Technical characteristics

**Technology:** "One push" safety system (avoids hose whip)

**Operating pressure:** 2 to 16 bar


**Flow rate at 6 bar:** 3686 l/min ( $\Delta P = 0,6$  bar)

**ID Passage:** 11 mm

**Temperature:** -15°C to +70°C

**Construction:** Body : Stainless steel

**Highlight:** Anti-static, Excellent efficiency, Harsh conditions

	A (mm)	B (mm)	C (mm)	BSPP female thread	Parts Numbers
	101	37	26	G 3/8	ISI 111102
	102	37	26	G 1/2	ISI 111103
	110,5	37	30	G 3/4	ISI 111104