

6 38X42

Double open ended spanner

metric

Code
6068550

ETIM
EC002130

EAN
4010886606858

UNSPSC
27-11-17-06

Country of origin
Germany

eCl@ss
21-04-01-04

Customs tariff number
82041100



Article description

- Acc. to DIN 3110, ISO 3318, ISO 1085, ISO 10102
- With flat heads
- Satin non-glare finish
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Secure grip thanks to slim profile shaft
- Overloading indicated by deformation
- Top-grade industrial quality for the hardest of continuous use
- Chrome-vanadium steel 31CrV3

Article information

Contents (Qty of pieces)	1	Width of head 2 [mm]	86 mm
Net weight [kg]	0,784 kg	Head height 1 [mm]	10 mm
Total length [mm]	359 mm	Width of head 1 [mm]	77,0 mm
Total width [mm]	84 mm	Width across flats [mm]	38x42
Total height [mm]	10 mm	Width across flats 2 [mm]	42
Material	31CrV3	Mouth position 1	15°
Standard	not standardised		
Width across flats 1 [mm]	38	Mouth position 2	not standardised