

Features

- **Scissor Action Mechanism** – Features a **25 mm jaw size** with an easy-to-use **scissor action** design for secure and reliable locking at isolation points.
- **Double Locking Tamper-Proof Design** – Equipped with an **interlocking shackle mechanism** that prevents unauthorized removal, enhancing security during lockout procedures.
- **Multi-User Locking** – Can accommodate **up to 6 padlocks**, allowing multiple workers to apply their own locks for group lockout operations.
- **Wide Padlock Compatibility** – Accepts padlocks with **shackle diameters up to 10 mm**, making it compatible with a broad range of safety padlocks.
- **Rugged Steel Construction** – Built from **durable steel** with a **red powder-coated finish** for improved corrosion resistance and high visibility in industrial settings.

RS PRO Standard Hasp - Small (25mm) - Double Locking

RS Stock No.: 0710523



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *This lockout hasp features a tamper-proof, interlocking design that ensures secure application during maintenance, effectively preventing unauthorized access.*
- *The scissor-style mechanism offers quick and easy placement around lockout points, with a 25 mm jaw size ideal for various industrial isolation points.*
- *Supports up to **6 personal lockout padlocks**, allowing multiple workers to lock the same device and maintain individual control during group maintenance tasks.*
- *Compatible with padlocks having shackles up to 10 mm in diameter, accommodating a wide range of lockout padlocks.*
- *Made from robust steel with a **red powder-coated finish**, offering excellent durability, corrosion resistance, and high visibility in demanding industrial environments.*
- *Ensures machinery and equipment remain securely de-energized during maintenance or servicing, promoting compliance with OSHA LOTO protocols.*

General Specifications

Type	Lockout Hasp
Material	Mild Steel
Colour	Red
Padlock holes	06
Package	LD + Paper Box

Mechanical Specifications

Dimensions	25mm X 39mm X 116mm
Dia (Jaw Size)	25mm
Body - Width	39mm
Body - Height	116mm
Weight	78 Grams

Operation Environment Specifications

Withstand temperature	-20°C to 90°C
-----------------------	---------------