



Humfree Contactor 40A, 4NO, 24V

ESD440S

Technical Properties

Rated current	40 A
Rated operational voltage Ue	400 V
Frequency	50/60 Hz
type of connection	with screw
Connection cross-sect. rigid cable	4 / 25mm ²
Connection cross-sect. flexible cable	4 / 16mm ²
Command voltage AC	24 V
Rigid cable connect. cross-sect. for control	1 to 10 mm ²
Max cable connect. cross section (flexible) for control	1 to 6 mm ²
Number of mechanical operations	1000000
Electric endurance in number of cycles	30000
Operating temperature	-10 to 50 °C
Storage temperature	-40 to 80 °C
Protection class	isol.class II
Protection index IP	2
Number of modules	3