



- Low Profile Plug

- High Performance Patch Cord

- Individually Packed With Test Results

**Product Description**

Copper patch cords are a critical component to ensuring the end to end performance of a network. HellermannTyton's patch cords are manufactured and tested to the highest quality to meet the component compliant requirements of the ISO/IEC 11801 and ANSI/TIA/EIA 568-C.2 standards.

The patch cords incorporate a low plug suitable for high density applications with an integral strain relief boot to minimise forces on the terminations and to manage the bend radius of the cable.

Cable are sheathed in LSOH material making them suitable for internal use.

**Features and Benefits**

- High performance
- Low profile shielded plug - ideal for Data Centre applications, blade servers, etc.
- Manufactured and tested to meet component compliant requirements of ISO/IEC 11801 and ANSI/TIA/EIA 568-C.2-1 Cat6 standard
- UK Manufactured
- Individually packed with test results
- Standard lengths: 1m, 2m, 3m, 5m, 10m
- Other lengths, colours and types available on request



Product Description	Ordering Code	UNS Number
Copper Patch Cord Cat6 LSOH 0.5m	RJ45NGB-0.5MGY	Available on request
Copper Patch Cord Cat6 LSOH 1.0m	RJ45NGB-1.0MGY	Available on request
Copper Patch Cord Cat6 LSOH 2.0m	RJ45NGB-2.0MGY	Available on request
Copper Patch Cord Cat6 LSOH 3.0m	RJ45NGB-3.0MGY	Available on request
Copper Patch Cord Cat6 LSOH 5.0m	RJ45NGB-5.0MGY	Available on request

**Test results**



**Connecting Hardware Test**

Tested from: 1 MHz  
 Tested to: 250 MHz  
 Standard: ISO/IEC 11801 and  
 ANSI/TIA/EIA 568-C.2-1  
 Limits: Cat6 - Connector

**Forward direction (A-B)**



**Reverse direction (B-A)**



Tel: +44 (0) 1604 707420  
 Web: www.htdata.co.uk  
 Email: sales@htdata.co.uk