

Features

- 1 Gang
- Twin Terminals Provided.
- Flex Outlet
- Cord Restraint

RS PRO Connection Plates

RS Stock No.: 0845496



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Safely cover electrical connections*
- *Fits standard 16mm 1 gang back boxes*
- *Urea mouldings make the plate suitable for use in applications where Antibacterial & Antiviral Certified material is required*
- *Suitable for use with flush and surface mount wiring accessories back boxes.*

General Specifications

Plate Dimensions (mm)	86 (W) x 86 (H) x 9.5 (D)
Plate Fixing Centres (mm)	60.3
Style	Rounded Profile
Anti Microbial Certified	Yes
Warranty (Years)	25

Mechanical Specifications

Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Torque Value (Nm)	1.8
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4
Twin Earth Terminals	Yes
Flex Outlet Available	Yes
Flex Outlet Location	Front & Bottom of Plate
Flex Outlet Dimension (mm)	Ø10
Minimum Back Box Depth (mm)	16
Ingress Protection	IP20
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Frequency (Hz)	50
Resistive Load Rating (A)	20

Approvals

Standards Met	BS 5733
---------------	---------