

Portable Band Saw LXT®

DPB183

18V • 66 mm • 0 - 3.2 m/s

Safe, non-sparking metal cutting

Cordless band saw for non-sparking metal cutting. Sawing capacity 66 x 66 mm. Brushless motor with adjustable speed 0–3.2 m / s. Sturdy and torsionally rigid aluminum frame ensures straight saws.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Blade Diametre	13 x 0,5 x 835 mm
Blade rapidity	0 - 3,2 m/s
Electronic brake	✓
Max. Cutting Capacity in Steel Pipe	66 x 66 mm
Sound Power Level (L _{WA})	89 dB(A)
Sound Pressure Level (L _{pA})	81 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Cutting metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting metal	1,5 m/s ²
Product Dimensions (L x W x H):	392 x 174 x 242 mm

User benefits

- LED light illuminates the work site
- The rubber coating on the handle ensures a firm working grip
- The standard electronics keep the speed constant even under load.
- Variable speed trigger allows operator to adjust speed based on materials or application
- Brushless maintenance-free and long-life motor
- Battery protection system automatically shuts off power when the battery level is low
- Cutting metal quickly and without sparks.

Link to product - www.makitauk.com



Related products

■ Optional AC

194514-0

Side Grip For Angle Grinder 115 - 150



■ Other

User manual

Parts drawing