

## Features

- AC mains rated
- High current rating, up to 10A
- Moulded black housing
- Modern rocker design
- Rated to UL 94 V-2
- Industry standard cut-out
- IP65 with an integral sealing gasket for extra protection
- Connection via 6.3 mm quick connect male tab terminals
- DPST switching configurations
- On-Off switching operation

## RS PRO Rocker Switches

RS Stock No.: 0119705



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

*An extensive range IP65 of double pole rocker switches designed for panel mounting. With a choice of illuminated and non-illuminated actuators in various legend designs and colours, the sealed rocker switch is suitable for a wide variety of applications.*

- Easy fitting, once the recommended panel cut-out is made, the robust rocker switches Snap-in to the panel and is held in place by the retention ribs ensuring a tight fit.*
- This waterproof rocker switch is available with momentary or latching formats including 2 and 3 position switching, On-Off, centre off and change over.*
- The fully sealed IP65 rocker switch is ideal for maintenance and repair in harsh environments including Class II appliances.*

## General Specifications

Contact Configuration	DPST
Switches Operation	On - Off
Panel Cut Out Width	22.2mm
Panel Cut Out Height	30.4mm
Contact Current Rating	10 A
Mounting Type	Panel Mount
Terminal Type	Quick Connect
Illuminated	No
Actuator Material	PC
Mechanical Life	10000 Operations
Contact Material	Silver-Tin Oxide Alloy
Standards Met	UL, cUL, Demko, ENEC
Bushing Style	Keyway (Threaded)
Housing	Nylon 66
Terminals	4

## Electrical Specifications

Contact Current Rating	10A at 125V ac
Voltage Rating	125V
Contact Resistance	50m Ohms Max.
Minimum Insulation Resistance	DC 500V 100M ohms
Dielectric Strength	AC 1500V 1 minute

## Mechanical Specifications

Panel Cut Out Width	22.2mm
Panel Cut Out Height	30.4mm
Actuator Length	36mm
Panel Cut Out Size	30.4x22.2mm
Bushing Length	10.6mm

## Operation Environment Specifications

Minimum Operating Temperature	-25°C
Maximum Operating Temperature	85°C

## Protection Category

IP Rating	IP65
-----------	------

## Approvals

Compliance/Certifications	UL, cUL, Demko, ENEC
Declarations	RoHS, REACH

