

A813 - Extended Length Nitrile Gauntlet

Collection: Chemical Protection Gloves

Range: Hand Protection

Materials: Nitrile

Inner Pack: 12

Outer Carton: 96

Product information

This extra-long 48cm chemical gauntlet offers excellent protection against many solvents. Designed with an anti-slip pattern, the A813 offers good grip in wet and dry conditions. The 0.55mm thickness ensures good abrasion resistance. Suitable for a range of industries such as industrial maintenance, offshore drilling, printing and chemical.

Chemical Protection Gloves

Working environments using hazardous chemicals and substances can be extremely harmful to workers and the correct protection is a must. Portwest supplies a range of gloves which are fully tested and certified to protect from a range of chemicals.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020

EN 388: 2016 + A1: 2018 (41X2X)

EN ISO 374-1:2016 + A1:2018 Type A (AGJKLMNOPST)

EN ISO 374-5:2016 Micro Organisms



Features

- Silicone free - Ideal for manufacturing, paint applications, electronics and glass handling where silicone is problematic
- Textured pattern for enhanced grip
- Suitable for use in chemical, oil and food industries
- Approved for safe food handling
- 0.55mm thickness
- 480mm length
- CE certified
- Chemical resistant gauntlet
- CE-CAT III
- Retail tag which aids presentation for retail sales
- Chemical resistant



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A813 - Extended Length Nitrile Gauntlet

Commodity Code: 4015190000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/10139-03/E05-01

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A813GNRM	Green	61.0	33.0	25.0	0.1680	0.0503	5036108324514	15036108813329
A813GNRL	Green	61.0	33.0	25.0	0.1760	0.0503	5036108324507	15036108813312
A813GNRXL	Green	61.0	33.0	25.0	0.1900	0.0503	5036108324521	15036108813336
A813GNRXXL	Green	61.0	33.0	25.0	0.2060	0.0503	5036108324538	15036108813343