



175
LUMEN



3-6H
RUNTIME



18M
RANGE




IP20/IK07
IP RATING

NEW IL-175R - SLIM RECHARGEABLE POCKET INSPECTION LIGHT

- 175 Lumen white COB LED, 6500k
- Secondary rear 150 lumen white COB LED, 6500k
- Extra top torch - 70 lumen SMD LED, 6500k
- Ultra compact pocket size
- 180° vertical folding head
- Super tough IK07 copolymer and aluminium construction
- Useful pocket clip
- Strong magnetic base and dual rear magnets
- High quality 350mAh li-ion battery
- Quick 1A USB Type-C charging - 2½ hours charge time
- 1m high quality USB Type-C cable included

BATTERY	3.7v 350mAh Li-ion Rechargeable Battery
WEIGHT	60g
DIMENSION	folded 111.5 x 19.2 mm / extended 225 x 19.2 mm

USB
TYPE-C



ADDITIONAL TOP TORCH



SECONDARY REAR COB LED