

Traditional external micrometer sets to cover a wide range of measurements.

Features

- Tungsten carbide measuring faces
- Satin-chrome forged steel frame with insulated grip
- Constant force ratchet on thimble
- Tapered for easier access to difficult areas
- Locking lever
- Adjusting key
- Standards: DIN 863
- Supplied in a wooden case with setting standards



MW215-01BL

MW215 Series Specification - Metric

Code No	Range (mm)	Resolution (mm)	Quantity
MW215-01BL	0-75	0.01	3 Micrometers In Set
MW215-02BL	0-100	0.01	4 Micrometers In Set
MW215-03BL	0-150	0.01	6 Micrometers In Set
MW215-04BL	0-200	0.01	8 Micrometers In Set

MW215 Series Specification - Imperial

Code No	Range (inch)	Resolution (inch)	Quantity
MW215-01BI	0-3	0.001	3 Micrometers In Set
MW215-02BI	0-4	0.001	4 Micrometers In Set
MW215-03BI	0-6	0.001	6 Micrometers In Set
MW215-04BI	0-8	0.001	8 Micrometers In Set