



COBARib Standard



COBARib Standard



COBARib Wide



## COBARib Anti-slip fluted rubber matting

- Durable, manufactured from hardwearing natural rubber.
- Fine ribbed surface has effective slip-resistance.
- Provides insulation from cold concrete floors.
- Has some noise insulation properties.
- Can also be used on workbenches.
- Available in a chunky COBARib Wide option.

### Technical Specification

<b>Material:</b>	Natural rubber
<b>Surface Finish:</b>	Fine fluted ribbed surface
<b>Product Height:</b>	3mm or 6mm
<b>Operating Temperature:</b>	-20°C to +80°C
<b>Resistant to Chemicals:</b>	Resistant to water and most mild acids
<b>Environmental Resistance:</b>	Use in wet or dry areas
<b>UV Resistance:</b>	Yes
<b>Typical Applications:</b>	Industrial uses around benches, workstations and walkways. Also suitable for use as a covering for bench work surfaces
<b>Installation Method:</b>	Loose lay
<b>Cleaning Method:</b>	Hose down or pressure wash using a mild detergent
<b>Country of Origin:</b>	China

Standard	3mm	Weight	6mm	Weight
0.9m x 10m	RR010010	26.00 kg	RR010030	63.80 kg
0.9m x per linear metre	RR010010C	2.60 kg	RR010030C	6.38 kg
1.2m x 10m	RR010020	34.00 kg	RR010040	85.20 kg
1.2m x per linear metre	RR010020C	3.40 kg	RR010040C	8.52 kg

Wide	3mm	Weight	6mm	Weight
0.9m x 10m	RR010010W	30.00 kg	RR010030W	79.40 kg
0.9m x per linear metre	RR010010WC	3.00 kg	RR010030WC	7.94 kg
1.2m x 10m	RR010020W	43.90 kg	RR010040W	94.00 kg
1.2m x per linear metre	RR010020WC	4.39 kg	RR010040WC	9.40 kg

