

## **LH-10 ; ## 0...3 mWG ##; 4...20 mA, 2-W**

### **Level Probe Model LH-10**

Item number:

Quantity: 1 pcs.

Order code: LH-10-A-B##-GD-KG-ZZZ

W101-ZZZZZZ-F2D-GSE5

Overview: LH-10 ; ## 0...3 mWG ##; 4...20 mA, 2-W  
@ 10 ... 30 V DC; Accuracy: 0.25% of span (with pressure ranges < 250 mbar: 0.5% of span)  
G1/2B  
FEP cable Cable length: 5 m UB=BN, 0V=GN  
Specifications according to data sheet: PE 81.09

Details: Level Probe Model LH-10  
High performance version  
Specifications according to data sheet: PE 81.09  
Accuracy: 0.25% of span (with pressure ranges < 250 mbar: 0.5% of span)  
Permissible medium temperature: -10...+50°C (+14...+122°F); with FEP cable - 10...+85°C (+14...+185°F)  
Ingress protection: IP 68  
Special protection: Longitudinal water resistance  
Output signal: 4 ... 20 mA, 2-wire  
Measuring range: ## 0...3 mWG ##  
Process connection: G 1/2 B  
Special design features: FEP cable  
Cable length: 5 m  
WIKA standard  
Power supply: 10 ... 30 V DC  
Pin assignment: UB=BN, 0V=GN  
\*Made in Germany\* on label  
WIKA standard - specification according to data sheet