

**8028**
**lifting BOW shackles, hot forged carbon steel, galvanized**
**CE**
**TECHNICAL DATA**

- safety factor: 5
- heat treatment: normalizing
- traceability code

**LABORATORY TESTS**

- chemical analysis
- metallographic analysis
- tensile test

**AVAILABLE CERTIFICATES**

- Technical product specifications
- Test report UNI EN10204 type 2.2
- Inspection certificate UNI EN10204 type 3.1
- CE Declaration of Conformity



|  | art.    | Ø<br>mm | "     | WFL<br>kg | B x C<br>mm |
|-----------------------------------------------------------------------------------|---------|---------|-------|-----------|-------------|
| 080280105                                                                         | 8028 5  | 5       | 3/16  | 80        | 20x16       |
| 080280106                                                                         | 8028 6  | 6       | 1/4   | 100       | 24x20       |
| 080280108                                                                         | 8028 8  | 8       | 5/16  | 200       | 32x24       |
| 080280110                                                                         | 8028 10 | 10      | 3/8   | 300       | 40x33       |
| 080280112                                                                         | 8028 12 | 12      | 1/2   | 500       | 48x39       |
| 080280114                                                                         | 8028 14 | 14      | 9/16  | 600       | 56x46       |
| 080280116                                                                         | 8028 16 | 16      | 5/8   | 800       | 64x46       |
| 080280118                                                                         | 8028 18 | 18      | 11/16 | 950       | 71x59       |
| 080280120                                                                         | 8028 20 | 20      | 3/4   | 1100      | 80x65       |
| 080280122                                                                         | 8028 22 | 22      | 7/8   | 1500      | 88x72       |
| 080280125                                                                         | 8028 25 | 25      | 1"    | 2000      | 100x81      |
| 080280128                                                                         | 8028 28 | 28      | 1.1/8 | 2600      | 112x91      |
| 080280132                                                                         | 8028 32 | 32      | 1.1/4 | 3200      | 128x104     |
| 080280138                                                                         | 8028 38 | 38      | 1.1/2 | 4500      | 152x124     |